



FLOWave SAW flowmeter

- No obstacles inside the measuring tube, compact, lightweight and low energy consumption
- Conforms to hygienic requirements, CIP/SIP compatible
- Ideal for liquids with low or no conductivity
- Digital communication, parameter setting via communicator, display and Wi-Fi
- Optional: ATEX certification, II 3G/D

Product variants described in the data sheet may differ from the product presentation and description.

Can be combined with

	Type 8802 ELEMENT continuous control valve systems - overview	▶
	Type 8619 multiCELL - Multi-channel and multi-function transmitter/controller	▶
	Type 8647 AirLINE SP – electro-pneumatic automation system	▶
	Type ME43 Fieldbus gateway	▶

Type description

The Type 8098 flowmeter is part of the FLOWave product range. It is based on SAW (Surface Acoustic Waves) technology and is mainly designed for applications with the highest hygienic demands. This is achieved by using:

- suitable stainless steel materials
- a measuring tube free of any wetted parts except for the actual tube
- the ideal outer hygienic design.

FLOWave offers a range of integrated functions, including the advantages of flexibility, ease of cleaning, compact dimensions, lightweight, easy installation and handling, and is compliant with numerous standards.

Optimal measurement results can be achieved with homogeneous liquids, free of air and solid particles. For liquids with high viscosity, an integrated viscosity compensation can be activated. Gas and steam cannot be measured; however, their flow does not have any negative effect on the device or its operation and other liquids flowing through afterwards are measured correctly as before. Special functions derived from further process values (density factor, acoustic transmission factor) offer additional information about the particular liquid in use (for details, see chapter **“7.2. Special functions” on page 24**).

Table of contents

1. General technical data	4
1.1. About the FLOWave flowmeter.....	4
1.2. All versions.....	4
1.3. FLOWave L flowmeter.....	7
With or without industrial communication	7
With industrial communication (Ethernet version)	9
1.4. FLOWave S flowmeter	10
2. Approvals	12
2.1. Certification.....	12
2.2. Certificates.....	12
2.3. Pressure Equipment Directive.....	13
Device used on a pipe	13
3. Materials	13
3.1. Chemical Resistance Chart – Bürkert resistApp.....	13
3.2. Material specifications	14
FLOWave L flowmeter without industrial communication	14
FLOWave L flowmeter with industrial communication	15
FLOWave S flowmeter	16
4. Dimensions	17
4.1. Transmitter of the FLOWave L flowmeter without industrial communication	17
4.2. Transmitter of the FLOWave L flowmeter with industrial communication	17
4.3. Transmitter of the FLOWave S flowmeter	17
4.4. Flowmeter with clamp process connection	18
4.5. Flowmeter with aseptic collar flange (BF).....	19
4.6. Flowmeter with aseptic collar clamp (BKS)	20
5. Performance specifications	21
5.1. Medium temperature.....	21
5.2. Measurement deviation	21
6. Product installation	22
6.1. Installation notes.....	22
6.2. Selection of the nominal diameter	22
6.3. Mounting options.....	23
FLOWave L flowmeter.....	23
FLOWave S flowmeter	23
7. Product operation	24
7.1. Measuring principle	24
7.2. Special functions	24
8. Product design and assembly	25
8.1. Product assembly	25
9. Product accessories	26
10. Ordering information	26

10.1. Bürkert eShop – Easy ordering and quick delivery.....	26
10.2. Recommendation regarding product selection	26
10.3. Bürkert product filter.....	27
10.4. Bürkert 3D Model - Interactive Animation	27
10.5. Ordering chart FLOWave L flowmeter with or without industrial communication	28
Clamp acc. to DIN 32676 series B (ISO 1127) process connection for pipe acc. to DIN 11866 series B (ISO 1127).....	28
Clamp acc. to DIN 32676 series C (ASME BPE) process connection for pipe acc. to DIN 11866 series C (ASME BPE)....	29
10.6. Ordering chart FLOWave S flowmeter	31
Clamp acc. to DIN 32676 series B (ISO 1127) process connection for pipe acc. to DIN 11866 series B (ISO 1127).....	31
Clamp acc. to DIN 32676 series C (ASME BPE) process connection for pipe acc. to DIN 11866 series C (ASME BPE)....	32
10.7. Ordering chart accessories.....	33

1. General technical data

1.1. About the FLOWave flowmeter

The flowmeter Type 8098 consists of:

- either a flow sensor Type S097 and a transmitter Type SE98 (version FLOWave L flowmeter), which is available with or without industrial communication (the FLOWave L version with industrial communication, recognisable by the two M12 female connectors and the M12 male connector, is called the Ethernet version.)



- or a flow sensor Type S097 and a transmitter Type SE91 (version FLOWave S flowmeter)



1.2. All versions

The following data applies to all versions.

Product properties

Material

Please make sure the device materials are compatible with the fluid you are using.

Detailed information can be found in chapter [“3.1. Chemical Resistance Chart – Bürkert resistApp” on page 13.](#)

Detailed information on the materials can be found in chapter [“3.2. Material specifications” on page 14.](#)

Non wetted parts

Sensor housing Stainless steel 304/1.4301

Wetted parts

Measurement tube and clamp Stainless steel 316L/1.4435 with low delta ferrite content

Dimensions Detailed information can be found in chapter [“4. Dimensions” on page 17.](#)

Surface quality

Measurement tube (inner surface) • Ra < 0.8 µm (30 µin.) or
• Ra < 0.4 µm (15 µin.) (electro-polished) according to ISO 4288

Measurement tube (outer surface), housing Ra < 1.6 µm (excluding welding seams) according to ISO 4288

Measuring range

Volume flow rate measurement 0...1.7 m³/h up to 0...90 m³/h
Detailed information can be found in chapter [“10.5. Ordering chart FLOWave L flowmeter with or without industrial communication” on page 28](#) or [“10.6. Ordering chart FLOWave S flowmeter” on page 31.](#)

Temperature measurement -20...+140 °C (-4...+284 °F)

Special function • ATF: acoustic transmission factor

• DF: density factor

Active by default, deselectable upon request. Detailed information can be found in chapter [“7.2. Special functions” on page 24.](#)

Performance data

Volume flow rate measurement

Under reference conditions i.e. measuring fluid = water free from gas bubbles and solids, ambient and water temperature = 23 °C ± 1 °C (73.4 °F ± 1.8 F), and short refresh time, while maintaining turbulent or laminar flow profile, with the minimum inlet (40 x DN) and outlet (1 x DN) distances and the appropriate internal diameter of the pipes. Deviation from reference conditions can be adjusted through the use of a built-in correction K factor adjustment or Teach-in Procedure.

Measurement deviation

- From 10 % of full scale up to full scale: ± 0.4 % of the measured value
- From 1 % of full scale up to 10 % of full scale: ± 0.08 % of full scale

Detailed information can be found in chapter [“5.2. Measurement deviation” on page 21.](#)

Repeatability

- From 10 % of full scale up to full scale: ± 0.2 % of the measured value

Refresh time

Selectable:

- Very short (~ 30 ms)
- Short (~ 55 ms)
- Long (~ 100 ms)

Temperature measurement

Measurement deviation

- For $T^\circ \leq 100$ °C (+212 °F): ± 1 °C (+ 1.8 °F)
- For 100 °C (+212 °F) $< T^\circ < 140$ °C (+284 °F): ± 1.5 %

Refresh time

Approx. 0.1 s

Electrical data

Operating voltage

The minimum voltage to be supplied depends on the fluid temperature and on the ambient operating temperature.

Detailed information can be found in chapter [“5.1. Medium temperature” on page 21.](#)

- 12...35 V DC filtered and regulated,
- Tolerance: ± 10 %
- Connection to main supply: permanent (through external SELV (Safety Extra Low Voltage) and LPS (Limited Power Source) power supply)

Power Source (not supplied)

Limited power source according to UL/EN 60950-1 standards or limited energy circuit according to UL/EN 61010-1 §9.4

DC reverse polarity protection

Yes

Voltage supply cable

For cable glands

- 0.2...1.5 mm² cross-section
- In nickel plated brass:
 - Cable with maximum operating temperature greater than +90 °C (+194 °F)
 - 5...14 mm diameter, shielded cable
- In stainless steel:
 - Cable with maximum operating temperature greater than +100 °C (+212 °F)
 - 6...12 mm diameter, shielded cable

For 5 pin M12 male connector (A-coded)

- Cable with maximum operating temperature greater than +80 °C (+176 °F)
- 3...6.5 mm diameter, shielded cable,

For 4 pin M12 female connector (D-coded)

- 0.75 mm² cross-section to connect to 5 pin M12 female connector (A-coded, not supplied)
- Cable with maximum operating temperature greater than +90 °C (+194 °F)
- 5e / CAT-5 min. category, 100 m max. length, shielded conductor with minimum STP

Medium data

Fluid

Non-dangerous liquids complying with article 4, §1 of 2014/68/EU directive. Detailed information can be found in chapter [“2.3. Pressure Equipment Directive” on page 13.](#)
By default the FLOWave flowmeter is set for a fluid with a sound velocity between 1000 m/s and 2000 m/s⁴⁾.

Temperature

- -20...+110 °C (-4...+230 °F). The maximum fluid temperature can be restricted by the ambient operating temperature.
- Max. conditions for sterilisation process: up to +140 °C (+284 °F) (+130 °C (+266 °F) for ATEX version) for max. 60 min
- Maximum temperature gradient: 10 °C/s (18 °F/s) (measured by the integrated sensor on the device)

Pressure (max.)

DN / Pipe standard	DIN 11850	ISO 1127	ASME BPE
DN 08, DN 10, ⅜", ½"	PN 25	PN 25	PN 25
DN 15, ¾", DN 25, 1"	PN 25	PN 25	PN 25
DN 40	PN 25	PN 16	–
1½", DN 50, 2"	PN 16	PN 16	PN 16

Process/Port connection & communication

Process connection/pipe size according to

DIN 32676 series A (DIN 11850)	DN 10, DN 15, DN 25, DN 40 and DN 50
DIN 32676 series B (ISO 1127)	DN 08, DN 15, DN 25, DN 40 and DN 50
DIN 32676 series C (ASME BPE)	⅜", ½", ¾", 1", 1½" and 2"
DIN 11864-2 Form A series A (DIN 11850)	Aseptic collar flange (BF) ¹⁾ : DN 15, DN 25, DN 40 and DN 50
DIN 11864-2 Form B (ISO 1127)	Aseptic collar flange (BF) ¹⁾ : DN 08, DN 15, DN 25, DN 40 and DN 50
DIN 11864-2 Form A series C (ASME BPE)	Aseptic collar flange (BF) ¹⁾ : ½", ¾", 1", 1½" and 2"
DIN 11864-3 Form A series A (DIN 11850)	Aseptic collar clamp (BKS) ¹⁾ : DN 15, DN 25, DN 40 and DN 50
DIN 11864-3 Form B (ISO 1127)	Aseptic collar clamp (BKS) ¹⁾ : DN 08, DN 15, DN 25, DN 40 and DN 50
DIN 11864-3 Form A series C (ASME BPE)	Aseptic collar clamp (BKS) ¹⁾ : ½", ¾", 1", 1½" and 2"
SMS 3017 (SMS 3008)	DN 25, DN 40 and DN 50
Device status	LED light ring according to NAMUR NE 107

Approvals and Certificates

Standards

Protection class ²⁾	IP65, IP67 (according to IEC/EN 60529), NEMA 4X (according to NEMA250), if the product is wired and if the cable glands are tightened and the covers are screwed tight. Unused cable glands must be sealed with the stopper gaskets provided (mounted upon delivery of the product). An unused M12 fixed connector must be protected by the screwed plug.
--------------------------------	---

Directives

CE directives	The applied standards, which verify conformity with the EU Directives, can be found on the EU Type Examination Certificate and/or the EU Declaration of conformity (if applicable).
Pressure equipment directives	Complying with Article 4, Paragraph 1 of 2014/68/EU directive Detailed information on the pressure equipment directive can be found in chapter "2.3. Pressure Equipment Directive" on page 13.

Certificate	• FDA declaration of conformity • Inspection certificate 3.1 • Certification of compliance ASME BPE • Calibration certificate • On request: – USP class VI declaration – ECR1935/2004 declaration – EAC declaration of conformity – Test report 2.2 – Certification of conformity for the surface quality DIN 4762, EN ISO 4287, EN ISO 4288 – Certification of conformity for passivation and electropolishing processes – MTBF (Mean Time Between Failures) manufacturer declaration
-------------	---

Certification	• EHEDG (Type EL - CLASS I)³⁾ • 3A (28-06) • UL-Listed for USA and Canada • ATEX
---------------	--

Environment and installation

Ambient temperature

Depends on the fluid temperature. Detailed information can be found in chapter **"5.1. Medium temperature"** on page 21.

Storage	-20...+70 °C (-4...+158 °F)
---------	-----------------------------

Relative air humidity	≤ 85 %, without condensation
Height above sea level	Max. 2000 m
Operating conditions	Continuous
Equipment mobility	Fixed device
Application range	Indoor and outdoor (protect the device against electromagnetic interference, ultraviolet rays and, when installed outdoors, against the effects of climatic conditions)
Installation category	Category I according to UL/EN 61010-1
Pollution degree	Degree 2 according to UL/EN 61010-1

1.) in German: BF = Bundflansch, BKS= Bundklemmstutzen

2.) Not evaluated by UL

3.) The EHEDG compliance for Clamp DIN 32676 is only valid if used in combination with gaskets from Combifit International B.V.

4.) Customer-specific setting on request. Please contact Bürkert partners!

1.3. FLOWave L flowmeter

The FLOWave L flowmeter is available in four variants of the transmitter:

- Stainless steel transmitter with nickel plated brass cable glands and M12 male connector
- Stainless steel transmitter with stainless steel cable glands and M12 male connector (full stainless steel version)
- Stainless steel transmitter with stainless steel M12 female and male connectors and industrial communication (Ethernet version)
- Stainless steel transmitter with stainless steel cable glands and M12 male connector (ATEX version).



With or without industrial communication

The following data applies to all versions (unless specified differently).

Product properties

Material

Detailed information on the materials can be found in chapter [“3.2. Material specifications” on page 14.](#)

Non wetted parts

Transmitter housing, blind cover	Stainless steel 304/1.4301
Seal	VMQ silicone (Methyl Vinyl Silicone)
Display	Float glass, stainless steel 304/1.4301
Cable glands	Nickel plated brass or stainless steel 304L/1.4307 or 316L/1.4404
Blind plugs	Black POM (polyoxymethylene) or PA6
4 pin M12 female connector and screwed plug	Stainless steel 304L/1.4307
5 pin M12 male connector and screwed plug	Nickel plated brass or stainless steel 316L/1.4404
Pressure compensating element	Diaphragm in ePTFE, O-ring in silicone 60 Shore A, body in stainless steel
Display module	2.4", monochrome graphic (240 × 160 pixels) German, English, French languages

Wi-Fi module Approved for Europe, USA and Canada)

- Can be used with or without display module
- Wi-Fi module (wireless standard 802.11b/g/n) with integrated web server, offers the same setting options as the display
- Transmission power: approx. 50 mW
- Radio range limited to approx. 10 m
- Integration into existing Wi-Fi infrastructure possible

Requirements:

- Windows 7, 8.1 or 10: IE11, Edge, Google Chrome, from version 53
- Android: Google Chrome, from version 53
- Apple: Safari, from iOS 9.3.5

Weight	DN 08, DN 10, 3/8", 1/2"	DN 15, 3/4"	DN 25, 1"	DN 40, 1 1/2"	DN 50, 2"
Clamp	Approx. 2.1 kg	Approx. 2 kg	Approx. 2.2 kg	Approx. 3 kg	Approx. 3.2 kg
Flange	Approx. 2.3 kg	Approx. 2.4 kg	Approx. 2.7 kg	Approx. 3.6 kg	Approx. 3.8 kg

Performance data

Frequency resolution	0.05 Hz over 0...2 kHz range
4...20 mA output uncertainty	± 0.04 mA
4...20 mA output resolution	0.8 µA

Electrical data

Power consumption	Without any consumption of output • For device with 2 x M20 x 1.5 cable glands and 1 x 5 pin M12 connector: max. 5 W • For device with 2 x 4 pin M12 connectors and 1 x 5 pin M12 connector, Ethernet version: max. 8 W • For device with 2 x 4 pin M12 connectors and 1 x 5 pin M12 connector, Ethernet version, with display and Wi-Fi module: max. 9 W
-------------------	---

Outputs

3 (1 digital, 1 analogue and 1 configurable: digital or analogue)	Valid for non-Ethernet versions only
Digital outputs	Overload information (through software diagnostics function) Transistor: • Type: NPN or PNP (wiring dependent), open collector, galvanically isolated • Operating modes: pulse (by default), On/Off, threshold, frequency (user configurable) • 0...2 kHz, 5...35 V DC, max. 700 mA, max. pulse duration: 2 s, selectable limits: 0.0001...10000 pulses/liter or 0.0001...9999.99 liters/pulse • Protected against polarity reversals of DC and overloads
Analogue output	Open loop detection (through software diagnostics function) Current: • 4...20 mA • 3.6 mA or 22 mA to indicate an error (only if 4...20 mA scale selected); galvanically isolated • Max. loop impedance: 1300 Ω at 35 V DC, 1000 Ω at 30 V DC, 700 Ω at 24 V DC, 450 Ω at 18 V DC

Process/Port connection & communication

Electrical connection	2 x M20 x 1.5 cable glands and 1 x 5 pin M12 male fixed connector (A-coded) for non-Ethernet versions only
Data transfer	External communication through bUS (Bürkert system bus, CANopen protocol)

Environment and installation

Ambient temperature

Depends on the fluid temperature. Detailed information can be found in chapter **"5.1. Medium temperature"** on page 21.

Operation	• For device with 2 x M20 x 1.5 cable glands and 1 x 5 pin M12 connector: – -10...+70 °C (+14...+158 °F) or -10...+40 °C (+14...+104 °F) for ATEX version, if -20 °C (4 °F) ≤ fluid temperature ≤ 80 °C (176 °F), – The ambient temperature decreases linearly up to 40 °C (104 °F) at a fluid temperature of 140 °C (284 °F) or up to 30 °C (86 °F) at a fluid temperature of 130 °C (266 °F) for ATEX version, if fluid temperature > 80 °C (176 °F) • For device with 2 x 4 pin M12 female connectors and 1 x 5 pin M12 connector, Ethernet version: -10...+55 °C (+14...+131 °F)
-----------	--

With industrial communication (Ethernet version)

Process/Port connection & communication	
Electrical connection	2 × 4 pin M12 female fixed connectors (D-coded) and 1 × 5 pin M12 male fixed connector (A-coded)
Industrial Communication	
Supported network protocols	• Modbus TCP • PROFINET • EtherNet/IP • EtherCAT
LEDs	• 2 Link/Act LEDs (green) • 2 Link LEDs (yellow)
Modbus TCP protocol	
Protocol	Internet protocol, version 4 (IPv4)
Network topology	• Tree • Star • Line (open daisy chain)
IP configuration	• Static IP address • Not supported: BOOTP (Bootstrap Protocol), DHCP (Dynamic Host Configuration)
Transmission speed	10 or 100 MBit/s
PROFINET protocol	
PROFINET IO specification	V2.3
Network topology	• Tree • Star • Ring (closed daisy chain) • Line (open daisy chain)
Network management	• LLDP (Link Layer Discovery Protocol) • SNMP V1 (Simple Network Management Protocol) • MIB (Management Information Base) • DCP (Discovery and Configuration Protocol)
IP configuration	• Manual (Device naming and IP setting)
Transmission speed	100 MBit/s full duplex
Maximum supported conformance class	CC-B
Media Redundancy (for ring topology)	MRP client is supported
GSDml file	See “Device Description Files” on the website in the Software chapter Type 8098 ►
EtherNet/IP protocol	
Protocol	Internet protocol, version 4 (IPv4)
Network topology	• Tree • Star • Ring (closed daisy chain) • Line (open daisy chain) • Linear (open Daisy Chain)
IP configuration	• Static IP address • BOOTP (Bootstrap Protocol) • DHCP (Dynamic Host Configuration Protocol)
Transmission speed	10 or 100 MBit/s
Duplex modes	Half duplex, full duplex, auto-negotiation
MDI modes (Medium Dependant Interface)	Auto-MDIX
Predefined standard objects	Identity, Message Router, Assembly, Connection Manager, DLR, QoS, TCP/IP Interface, EtherNet Link object
EDS file	See “Device Description Files” on the website in the Software chapter Type 8098 ►
EtherCAT protocol¹⁾	
Industrial Ethernet interface X1, X2	X1: EtherCAT IN, X2: EtherCAT OUT
Maximum number of cyclic input/output data	512 bytes in total

Maximum number of cyclic input data	1024 bytes
Maximum number of cyclic output data	1024 bytes
Acyclic communication (CoE)	• SDO • SDO master-slave • SDO slave-slave (depends on master capacity)
Type	Complex slave
Fieldbus Memory Management Units (FMMUs)	8
Sync Managers	4
Transmission speed	100 Mbit/s

Approvals and Certificates

Certification	• PROFINET • EtherNet/IP
---------------	---

1.) EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH.

1.4. FLOWave S flowmeter

The FLOWave S flowmeter is available in two variants of the transmitter:

- Stainless steel transmitter without output and with stainless steel 5 pin M12 connector
- Stainless steel transmitter with 2 configurable outputs (DO/AO) and stainless steel 8 pin M12 connector.



Product properties

Material

Detailed information on the materials can be found in chapter [“3.2. Material specifications” on page 14.](#)

Non wetted parts

Transmitter housing, cover	Stainless steel 304/1.4301
Light guide	PC (Polycarbonate) and O-ring in EPDM (Ethylene Propylene Diene Monomer)
Seal between sensor and transmitter	VMQ silicone (Methyl Vinyl Silicone)
5- or 8-pin M12 male connector and screwed plug	Stainless steel 316L/1.4404 or 303/1.4305

Weight	DN 08, DN 10, 3/8", 1/2"	DN 15, 3/4"	DN 25, 1"	DN 40, 1 1/2"	DN 50, 2"
Clamp	Approx. 1.7 kg	Approx. 1.9 kg	Approx. 2.1 kg	Approx. 2.4 kg	Approx. 3.1 kg
Flange	Approx. 1.9 kg	Approx. 2.3 kg	Approx. 2.6 kg	Approx. 3.0 kg	Approx. 3.7 kg

Electrical data

Power consumption	• For device without output: max. 2.5 W • For device with 2 outputs (DO/AO): max. 5 W
-------------------	--

Outputs

2, each configurable as digital or analogue output

Digital output

Only for device with 8-pin M12 connector

Overload information (through software diagnostics function)

Transistor:

- Type: NPN or PNP (wiring dependent), open collector, galvanically isolated
- Operating modes: pulse (by default), On/Off, threshold, frequency (user configurable)
- 0...2 kHz, 5...35 V DC, max. 700 mA, max. pulse duration: 2 s, selectable limits: 0.0001...10000 pulses/litre or 0.0001...9999.99 litres/pulse
- Protected against polarity reversals of DC and overloads

Analogue output

Open loop detection (through software diagnostics function)

Current:

- 4...20 mA
- 3.6 mA or 22 mA to indicate an error (only if 4...20 mA scale selected); galvanically isolated
- Max. loop impedance: 1300 Ω at 35 V DC, 1000 Ω at 30 V DC, 700 Ω at 24 V DC, 450 Ω at 18 V DC

Process/Port connection & communication

Electrical connection

- 1 x 5 pin M12 male fixed connector (A-coded) for device without output
- 1 x 8 pin M12 male fixed connector (A-coded) for device with 2 outputs

Data transfer

- Device without output: external communication through bÜS (Bürkert system bus, CANopen protocol)
- Device with 2 outputs: bÜS connection only to the Bürkert Communicator for configuration and software update of the device. Due to the missing CAN shield the conventional bÜS/ CANopen communication is not recommended.

Environment and installation

Ambient temperature

Depends on the fluid temperature. Detailed information can be found in chapter [“5.1. Medium temperature” on page 21](#).

Operation

- -10...+70 °C (+14...+158 °F) if -20 °C (4 °F) $\leq$ fluid temperature $\leq$ 80 °C (176 °F)
- The ambient temperature decreases linearly up to 40 °C (104 °F) at a fluid temperature of 140 °C (284 °F), if fluid temperature > 80 °C (176 °F),

2. Approvals

Note:

- The certification/certificate listed below must be stated when making enquiries. This is the only way to ensure that the product complies with all required specifications.
- Not all available devices can be supplied with the certification/certificate below.

2.1. Certification

Certificate	Description
	EHEDG (Type EL - CLASS I) The EHEDG compliance is only valid if used in combination with gaskets from Combifit International B.V.
	3-A Sanitary Standards The 8098 meets sanitary standards for design and fabrication. Certificate authorization number: 1178
 Measuring Equipment E237737	UL-Listed for USA and Canada Products are UL-listed products and comply also with the following standards: • UL 61010-1 • CAN/CSA-C22.2 No.61010-1 Certificate number: 2017-10-27-E237737
	LCIE 20 ATEX 1004 X Specifications Ex • II 3G Ex ec IIC T4 Gc • II 3D Ex tc IIIC T110 °C Dc or T130 °C Dc Measures to comply with ATEX requirements: refer to the Supplement ATEX Type 8098 ► under user manual. The Ex. certification is only valid if the Bürkert device is used as described in the supplement ATEX. If unauthorized changes are made to the device, the Ex. certification becomes invalid.
	PROFINET Certificate number: Z12446
	EtherNet/IP Document number: 11839

2.2. Certificates

Certificate	Description
	FDA The devices comply in their composition with the Code of Federal Regulations published by the FDA (Food and Drug Administration, USA).
	EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH

2.3. Pressure Equipment Directive

The device conforms to Article 4, Paragraph 1 of the Pressure Equipment Directive 2014/68/EU under the following conditions:

Device used on a pipe


Note:

- The data in the table is independent of the chemical compatibility of the material and the fluid.
- PS = maximum admissible pressure, DN = nominal diameter of the pipe

Type of fluid	Conditions
Fluid group 1, Article 4, Paragraph 1.c.i	$DN \leq 25$
Fluid group 2, Article 4, Paragraph 1.c.i	$DN \leq 32$ or $PS \cdot DN \leq 1000$
Fluid group 1, Article 4, Paragraph 1.c.ii	$DN \leq 25$ or $PS \cdot DN \leq 2000$
Fluid group 2, Article 4, Paragraph 1.c.ii	$DN \leq 200$ or $PS \leq 10$ or $PS \cdot DN \leq 5000$

3. Materials

3.1. Chemical Resistance Chart – Bürkert resistApp



Bürkert resistApp – Chemical Resistance Chart

You want to ensure the reliability and durability of the materials in your individual application case? Verify your combination of media and materials on our website or in our resistApp.


[Start Chemical Resistance Check](#)

3.2. Material specifications

FLOWave L flowmeter without industrial communication

Note:

The following picture describes a device with 2 x M20 x 1.5 cable glands, 1 x 5 pin M12 male connector and clamp process connection.




No.	Description	Material
1	Blind cover	Stainless steel 304/1.4301
2	Wi-Fi module	Float glass, stainless steel 304/1.4301
3	Display module	Float glass, stainless steel 304/1.4301
4	Multi-colour LED behind seal (used for e.g. to indicate the status of the product, based on the NAMUR NE 107 standard)	VMQ silicone
5	Transmitter housing	Stainless steel 304/1.4301
6a	Cable glands (full stainless steel version)	Stainless steel 304L/1.4307
6b	Cable glands	Nickel plated brass
6c	Cable glands (ATEX version)	Stainless steel 316L/1.4404
7a	Blind plug (full stainless steel version)	PA6
7b	Blind plug	Black POM
7c	Blind plug (ATEX version)	PA6
8	5 pin M12 male fixed connector (wired to bÜS) with screwed plug	Stainless steel 316L/1.4404 (if equipped with 6a) or Nickel plated brass (if equipped with 6b)
9	Functional earth	Cylinder screw, washer, washer spring: stainless steel A4 blind rivet nut: stainless steel 1.4578/A4
10	Seal	VMQ silicone
11	Blind cover	Stainless steel 304/1.4301
12	Sensor housing	Stainless steel 304/1.4301
13	Sensor measurement tube	Stainless steel 316L/1.4435 with low delta ferrite content
14	Process connection (either clamp connections or flange connections)	Stainless steel 316L/1.4435 with low delta ferrite content
15	Pressure compensating element	Diaphragm: ePTFE; support: polyester; O-ring: silicone 60 Shore A; body: stainless steel (316L/1.4404)

FLOWave L flowmeter with industrial communication

Note:

The following picture describes a device (Ethernet version) with 2 × 4 pin M12 female connectors, 1 × 5 pin M12 male connector and flange process connection.




No.	Description	Material
1	Blind cover or	Stainless steel 304/1.4301
2	Wi-Fi module	Float glass, stainless steel 304/1.4301
3	Display module	Float glass, stainless steel 304/1.4301
4	Multi-colour LED behind seal (used for e.g. to indicate the status of the product, based on the NAMUR NE 107 standard)	VMQ silicone
5	Transmitter housing	Stainless steel 304/1.4301
6	4 pin M12 female fixed connectors with screwed plug	Stainless steel 304L/1.4307
7	5 pin M12 male fixed connector (wired to bÜS) with screwed plug	Stainless steel 316L/1.4404
8	Functional earth	Cylinder screw, washer, washer spring: stainless steel A4 blind rivet nut: stainless steel 1.4578/A4
9	Blind cover	VMQ silicone
10	Seal	Stainless steel 304/1.4301
11	Sensor housing	Stainless steel 304/1.4301
12	Sensor measurement tube	Stainless steel 316L/1.4435 with low delta ferrite content
13	Process connection (either clamp connections or flange connections)	Stainless steel 316L/1.4435 with low delta ferrite content
14	Pressure compensating element	Diaphragm: ePTFE; support: polyester; O-ring: silicone 60 Shore A; body: stainless steel (316L/1.4404)

FLOWave S flowmeter

Note:

The following picture shows a device with 1 × 5 pin M12 male connector and clamp process connection.



No.	Description	Material
1	Cover	Stainless steel 304/1.4301
2	Light guide for status display behind seal (used for e.g. indicating the status of the product, based on the NAMUR NE 107 standard)	PC and O-ring in EPDM
3	Transmitter housing	Stainless steel 304/1.4301
4	5 pin M12 male fixed connector (wired to bÜS) with screwed plug or 8 pin M12 male fixed connector (wired to bÜS as service interface ^{1.)} and 2 x DO/AO) with screwed plug	Stainless steel 316L/1.4404 or 303/1.4305
5	Functional earth	Cylinder screw, washer, washer spring: stainless steel A4 blind rivet nut: stainless steel 1.4578/A4
6	Seal	VMQ silicone
7	Sensor housing	Stainless steel 304/1.4301
8	Sensor measurement tube	Stainless steel 316L/1.4435 with low delta ferrite content
9	Process connection (either clamp connections or flange connections)	Stainless steel 316L/1.4435 with low delta ferrite content


1.) bÜS connection only to the Bürkert communicator for configuration and software update of the device. Due to the missing CAN shield the conventional bÜS/ CANopen communication is not recommended.

4. Dimensions

4.1. Transmitter of the FLOWave L flowmeter without industrial communication

Note:


Specifications in mm



4.2. Transmitter of the FLOWave L flowmeter with industrial communication

Note:


Specifications in mm



4.3. Transmitter of the FLOWave S flowmeter

Note:


Specifications in mm



4.4. Flowmeter with clamp process connection

Note:

- Specifications in mm (unless specified differently)
- Clamp according to DIN 32676 series A, B or C, or SMS 3017



Clamp/pipe size		H1	H2	D1	D	D2	D3	G	L1	L
[mm]	[inch]									
Clamp according to DIN 32676 series A (DIN 11850) and process pipe according to DIN 11866 series A (DIN 11850)										
10	–	220	154	10.00	10.00	14.00	34.00	60.30	105	158
15 ^{1.)}	–	220	154	15.75	16.00	19.05	34.00	60.30	105	166
25 ^{1.)}	–	220	154	22.10	26.00	25.40	50.50	60.30	105	236
40 ^{1.)}	–	200	134	34.80	38.00	38.10	50.50	91.00	180	326
50 ^{1.)}	–	200	134	47.50	50.00	50.80	64.00	91.00	180	306
Clamp according to DIN 32676 series B (ISO 1127) and process pipe according to DIN 11866 series B (ISO 1127)										
08	–	220	154	10.30	10.30	14.00	25.00	60.30	105	158
15	–	220	154	18.10	18.10	21.30	50.50	60.30	105	168
15 ^{2.)}	–	220	154	18.10	18.10	21.30	34.00	60.30	105	168
25	–	220	154	29.70	29.70	33.70	50.50	60.30	120	175
40	–	200	134	44.30	44.30	48.30	64.00	91.00	180	273
50	–	200	134	56.30	56.30	60.30	77.50	91.00	180	273
Clamp according to DIN 32676 series C (ASME BPE) and process pipe according to DIN 11866 series C (ASME BPE)										
–	3/8	220	154	7.75	7.75	14.00	25.00	60.30	105	158
–	1/2	220	154	9.40	9.40	14.00	25.00	60.30	105	158
–	3/4	220	154	15.75	15.75	19.05	25.00	60.30	105	143
–	1	220	154	22.10	22.10	25.40	50.50	60.30	105	143
–	1 1/2	200	134	34.80	34.80	38.10	50.50	91.00	180	273
–	2	200	134	47.50	47.50	50.80	64.00	91.00	180	273
Clamp according to SMS 3017 and process pipe according to SMS 3008										
25 ^{1.)}	–	220	154	22.10	22.60	25.40	50.50	60.30	105	143
40 ^{1.)}	–	200	134	34.80	35.60	38.10	50.50	91.00	180	273
50 ^{1.)}	–	200	134	47.50	48.60	50.80	64.00	91.00	180	273

1.) DIN 32676 series A and SMS 3017 based on ASME BPE pipe dimension with adapted concentric clamp design


Design according to EHEDG DOC8 guidelines

2.) Similar to DIN 32676 series B but with clamp 34.0

4.5. Flowmeter with aseptic collar flange (BF)

Note:

- Specifications in mm (unless specified differently)
- Aseptic collar flange (BF) according to DIN 11864-2 form A series A, B or C




Flange/pipe size		H1	H2	TK	D1	D	D2	D3	G	L1	Lp	L
[mm]	[inch]											
Flange according to DIN 11864-2 series A (DIN 11850) and process pipe according to DIN 11866 series A (DIN 11850)												
15 ^{1.)}	–	220	154	42	15.75	16.00	19.05	59	60.30	105	163	166
25 ^{1.)}	–	220	154	53	22.10	26.00	25.40	70	60.30	105	237	240
40 ^{1.)}	–	200	134	65	34.80	38.00	38.10	82	91.00	180	327	330
50 ^{1.)}	–	200	134	77	47.50	50.00	50.80	94	91.00	180	307	310
Flange according to DIN 11864-2 series B (ISO 1127) and process pipe according to DIN 11866 series B (ISO 1127)												
08	–	220	154	37	10.30	10.30	14.00	54	60.30	105	155	158
15	–	220	154	45	18.10	18.10	21.30	62	60.30	105	170	173
25	–	220	154	57	29.70	29.70	33.70	74	60.30	120	187	190
40	–	200	134	71	44.30	44.30	48.30	88	91.00	180	275	278
50	–	200	134	85	56.30	56.30	60.30	103	91.00	180	262	265
Flange according to DIN 11864-2 series C (ASME BPE) and process pipe according to DIN 11866 series C (ASME BPE)												
–	½	220	154	37	9.40	9.40	14.00	54	60.30	105	155	158
–	¾	220	154	42	15.75	15.75	19.05	59	60.30	105	168	171
–	1	220	154	49	22.10	22.10	25.40	66	60.30	105	165	168
–	1½	200	134	62	34.80	34.80	38.10	79	91.00	180	275	278
–	2	200	134	75	47.50	47.50	50.80	92	91.00	180	275	278

1.) DIN 11864-2 series A based on ASME BPE pipe dimension with adapted concentric clamp design
Design according to EHEDG DOC8 guidelines

4.6. Flowmeter with aseptic collar clamp (BKS)

Note:

- Specifications in mm (unless specified differently)
- Aseptic collar clamp (BKS) according to DIN 11864-3 form A series A, B or C




Clamp/pipe size		H1	H2	D1	D	D2	D3	G	L1	Lp	L
[mm]	[inch]										
Clamp according to DIN 11864-3 series A (DIN 11850) and process pipe according to DIN 11866 series A (DIN 11850)											
15 ^{1.)}	-	220	154	15.75	16.00	19.05	34.00	60.30	105	163	166
25 ^{1.)}	-	220	154	22.10	26.00	25.40	50.50	60.30	105	237	240
40 ^{1.)}	-	200	134	34.80	38.00	38.10	64.00	91.00	180	327	330
50 ^{1.)}	-	200	134	47.50	50.00	50.80	77.50	91.00	180	307	310
Clamp according to DIN 11864-3 series B (ISO 1127) and process pipe according to DIN 11866 series B (ISO 1127)											
08	-	220	154	10.30	10.30	14.00	34.00	60.30	105	155	158
15	-	220	154	18.10	18.10	21.30	34.00	60.30	105	166	169
25	-	220	154	29.70	29.70	33.70	50.50	60.30	120	187	190
40	-	200	134	44.30	44.30	48.30	64.00	91.00	180	277	280
50	-	200	134	56.30	56.30	60.30	91.00	91.00	180	268	271
Clamp according to DIN 11864-3 series C (ASME BPE) and process pipe according to DIN 11866 series C (ASME BPE)											
-	½	220	154	9.40	9.40	14.00	34.00	60.30	105	155	158
-	¾	220	154	15.75	15.75	19.05	34.00	60.30	105	164	167
-	1	220	154	22.10	22.10	25.40	50.50	60.30	105	161	164
-	1½	200	134	34.80	34.80	38.10	64.00	91.00	180	275	278
-	2	200	134	47.50	47.50	50.80	77.50	91.00	180	276	279

1.) DIN 11864-3 series A based on ASME BPE pipe dimension with adapted concentric clamp design
Design according to EHEDG DOC8 guidelines

5. Performance specifications

5.1. Medium temperature



5.2. Measurement deviation

Note:

This table shows the measurement deviations according to the pipe connection standards per measuring range.

DN	Pipe standard	Flow velocity in sensor tube [m/s]	0.1	1	10
3/8"	ASME BPE	Volume flow rate range [m³/h]	0.017	0.17	1.7
			± 0.08 % of full scale	± 0.4 % of measured value	
1/2"	ASME BPE	Volume flow rate range [m³/h]	0.025	0.25	2.5
			± 0.08 % of full scale	± 0.4 % of measured value	
08 10	ISO 1127 DIN 11850	Volume flow rate range [m³/h]	0.03	0.30	3
			± 0.08 % of full scale	± 0.4 % of measured value	
3/4" 15	ASME BPE DIN 11850	Volume flow rate range [m³/h]	0.07	0.7	7
			± 0.08 % of full scale	± 0.4 % of measured value	
15	ISO 1127	Volume flow rate range [m³/h]	0.10	1.0	10
			± 0.08 % of full scale	± 0.4 % of measured value	
1" 25 25	ASME BPE DIN 11850 SMS 3008	Volume flow rate range [m³/h]	0.14	1.4	14
			± 0.08 % of full scale	± 0.4 % of measured value	
25	ISO 1127	Volume flow rate range [m³/h]	0.25	2.5	25
			± 0.08 % of full scale	± 0.4 % of measured value	
1 1/2" 40 40	ASME BPE DIN 11850 SMS 3008	Volume flow rate range [m³/h]	0.35	3.5	35
			± 0.08 % of full scale	± 0.4 % of measured value	
40	ISO 1127	Volume flow rate range [m³/h]	0.56	5.6	56
			± 0.08 % of full scale	± 0.4 % of measured value	
2" 50 50	ASME BPE DIN 11850 SMS 3008	Volume flow rate range [m³/h]	0.64	6.4	64
			± 0.08 % of full scale	± 0.4 % of measured value	
50	ISO 1127	Volume flow rate range [m³/h]	0.90	9.0	90
			± 0.08 % of full scale	± 0.4 % of measured value	

6. Product installation

6.1. Installation notes

Note:

The flowmeter is not designed for gas and steam flow measurement. However, their flow does not have any negative effect on the device or its operation. Other liquids flowing through again afterwards are measured correctly as before.

The factory calibration of the FLOWave is done under reference conditions with inlet (40xDN) and outlet (1 x DN) distances and the appropriate internal diameter of the pipes.

Deviation from reference conditions can be easily adjusted through the use of a built-in K factor adjustment or Teach in procedure. We can support you if necessary, please do not hesitate to contact us.

The device can be installed into either horizontal, oblique or vertical pipes. But an installation on a vertical pipe will be better to prevent air or gas bubbles inside the measurement area. **For proper operation always ensure a totally filled measurement tube.**

Conformity to 3A and EHEDG requires an angle of at least 5° (for SMS or series A connections) or 3° (all others available connections) against horizontal to ensure complete draining however this not necessary for proper operation of the FLOWave.

The suitable pipe size can be selected using the diagram for selecting the nominal diameter of the pipe. See chapter **"6.2. Selection of the nominal diameter"** on page 22.

6.2. Selection of the nominal diameter

The graph is used to determine the DN of the pipe and the flowmeter appropriate to the application, according to the fluid velocity and the flow rate. On the chart, the intersection of flow rate and flow velocity gives the appropriate diameter.

Example 1:


Flowmeter with process connection according to DIN 32676 series B (ISO 1127) or DIN 11864-2 form A series B

- Flow: 10 m³/h
 - Optimal flow rate: 1...3 m/s
- Result: Select a pipe size of DN 40 or DN 50

Example 2:

Flowmeter with process connection according to DIN 32676 series A (DIN 11850) or DIN 11864-2 series A (DIN 11850)


- Flow: 10 m³/h
 - Optimal flow rate: 1...3 m/s
- Result: Select a pipe size of DN 40 or DN 50



6.3. Mounting options

FLOWave L flowmeter

The product is delivered as described in position 1 in the picture below. The position of the transmitter can be changed in 90° steps. The position of the display module and the blind cover can also be changed in steps of 90° both on the top of the unit and on the front face.



Position 1

For safety reasons the display module and blind cover on the top or front are locked. The display module and blind cover can be unlocked with a magnetic key which is included in the delivery of each device.



FLOWave S flowmeter

The product is delivered as described in position 1 in the picture below. The position of the transmitter can be changed in 90° steps. For safety reasons the transmitter is locked. The transmitter can be unlocked with a magnetic key which is included in the delivery of each device.



Position 1

7. Product operation


7.1. Measuring principle

The technology used is based on SAW (Surface Acoustic Waves). The type of wave propagation is similar to what happens when an earthquake occurs in nature.

In the case of FLOWave it is a miniaturized signal, not running on the surface of the earth but on a measurement tube. FLOWave uses so called interdigital transducers which are placed on flattened areas of the tube surface. Each one acts as emitter as well as receiver. Two of them (nos. 1 and 4) emit forward, in the direction of the liquid flow, the others (nos. 2 and 3) backwards, i.e. in the opposite direction to the direction of flow. The propagation time is measured from emitter to receiver. The difference between the forward and backward propagation time of the waves is proportional to the volume flow rate.

The high performance measurement is based on:

- Each emitter creates multiple receiving signals at two other receivers
- The results are based on the reception of the signals that pass through the liquid one or more times.
- Several measurements can be performed based on the collected information. Many properties of the liquid can be derived, including the flow velocity, the fraction of the transmitted signal ("acoustic transmission factor"), and the so-called "density factor" (see below), as well as information about the presence of gas bubbles or solid parts.



This figure shows, as an example, the reception signals when interdigital transducer 1 is transmitting. The emitter excitation produces the SAW with a frequency of more than 1 MHz.

As a result of the emission of these waves, the following effects occur:

- A wave propagates along the surface of the tube (see orange line).
- A wave is emitted (see green line) and passes through the liquid towards the opposite side of the tube at a certain angle, which depends mainly on the speed of propagation on the surface of the tube and in the liquid.
- Upon reaching the opposite side of the tube, two effects take place.
 - A wave is triggered in the tube and propagates (see green line) to receiver 3
 - A wave is triggered in the liquid (see yellow line) and passes through it again to the opposite wall of the tube.

These effects get repeated at each reflection, resulting in all the different colour-coded signals indicated in the figure.

7.2. Special functions

For the detection of gas bubbles and solid particles the device (from firmware version 01.05.00) includes a so called "acoustic transmission factor" with a measurement range of 5...120 %. The value of this is continuously measured and is directly dependent on gas bubbles and solids in a fluid.

A "density factor", with a measuring range of 0.8...1.3, is available for the detection and differentiation of liquids. This continuously measured value, which uses water as reference fluid, is temperature-compensated and so its value is representative in a tight value range for each liquid. The changes in value of this process measurement enable differentiation between different liquids.

8. Product design and assembly


8.1. Product assembly

The 8098 flowmeter consists of a S097 flow sensor and a SE98 transmitter (FLOWave L flowmeter) or SE91 transmitter (FLOWave S flowmeter).

The flow sensor includes the measurement tube equipped with interdigital transducers, the sensor housing and the process connections in accordance to the standards ISO, ASME BPE, DIN, SMS. At present the sensor size ranges from DN 15 to DN 50 or from ¾" to 2".

The FLOWave L flowmeter is available with or without display. The high resolution display includes a capacitive working keypad for all interactive user actions, guided by a user friendly menu system. The output signals include one analogue output and one digital output; while a third output signal can be switched between analogue and digital through parameterization. Electrical connection is done on push-in connectors via two cable glands and/or one M12 connector.

The FLOWave S flowmeter is only available without display. The electrical connection is made via an M12 connector.



9. Product accessories

Note:

To set up a device without a display, please use the USB-büS interface, Type 8920 and for the FLOWave S with two outputs, the büS adaptor cable article no. 773286 is required too.

See **Software manual Type 8920** ► for more information.

Accessories	No.	Description
	1	Quick-Start
	2	Power supply: 100...240 V AC/ 24 V DC 1 A and adaptors for power supply worldwide use
	3	büS terminating resistor on büS Y-splitter
	4	5 pin M12 male connector wired on free end cable
	5	büS connection cable with 5 pin M12 plug, micro USB B plug
	6	büS adapter with 5 pin M12 plug, A-coded to 5 pin M12 plug, A-coded
	7	büS stick (USB to büS/CANopen adaptor)
	8	büS service cable with 5 pin M12 plug, mini USB and circular plug-in connectors for power supply
	9	Magnetic key
	10	CD - Communicator (30-day license without registration, update and licensing over Bürkert home page)

10. Ordering information

10.1. Bürkert eShop – Easy ordering and quick delivery



Bürkert eShop – Easy ordering and fast delivery

You want to find your desired Bürkert product or spare part quickly and order directly? Our online shop is available for you 24/7. Sign up and enjoy all the benefits.

[Order online now](#)

10.2. Recommendation regarding product selection

Note:


- The installation of the flowmeter in a pipe requires the use of counter-connection, seals, fixing elements, etc. depending on the used norm.
- The drawings show the installation with a standard version of the flow meter. The installation is also valid for the compact version.

For instance with middle-sized devices:

• With clamp according to DIN 32676

To insert a FLOWave DN 40 with clamps according to DIN 32676 series A (DIN 11850) (with $R_a < 0.8 \mu m$) to a pipe according to DIN 11866 series A (DIN 11850), the **correct adapters to be selected and separately ordered** are for instance


- 2 x **BBS-25** clamp ferrules, Article no. 747237, see **data sheet Type BBS-25** ► for more information
- 2 x the appropriate seals (not provided)
- 2 x the corresponding clamps, Article no. 731164



- **With aseptic collar flange (BF) according to DIN 11864-2 form A**

To insert a FLOWave DN 40 with collar flanges according to DIN 11864-2 series B (ISO 1127) (with $R_a < 0.8 \mu m$) to a pipe according to DIN 11866 series B (ISO 1127), the **correct adapters to be selected and separately ordered** are for instance


- 2x **BBS-06** aseptic groove flange, Article no. 731860, see **data sheet Type BBS-06** ► for more information
- 2x the appropriate seals (not provided)
- 8x the corresponding screws, flat washers and nuts (please refer to the DIN 11864-2 standard)



- **With aseptic collar clamp (BKS) according to DIN 11864-3 form A**

To insert a FLOWave 1" with hygienic collar clamps according to DIN 11864-3 series C (ASME BPE) (with $R_a < 0.8 \mu m$) to a pipe according to DIN 11866 series C (ASME BPE), the **correct adapters to be selected and separately ordered** are for instance

- 2x **BBS-05** aseptic groove clamp, Article no. 730272, see **data sheet Type BBS-05** ► for more information
- 2x the appropriate seals (not provided)
- 2x the corresponding clamps, Article no. 731164



10.3. Bürkert product filter



Bürkert product filter – Get quickly to the right product

You want to select products comfortably based on your technical requirements? Use the Bürkert product filter and find suitable articles for your application quickly and easily.

[Try out our product filter](#)

10.4. Bürkert 3D Model - Interactive Animation

Applications & Tools



Bürkert 3D Model - Interactive Animation

3D Model and Interactive Animation are available on the website of the flowmeter Type 8098.

See **website of the Type 8098** ► under “Applications and Tools”.

10.5. Ordering chart FLOWave L flowmeter with or without industrial communication

Clamp acc. to DIN 32676 series B (ISO 1127) process connection for pipe acc. to DIN 11866 series B (ISO 1127)

Note:

- To set up a device without a display, please use the USB-büS interface, Type 8920 (has to be ordered separately - see chapter "9. Product accessories" on page 26 and "10.7. Ordering chart accessories" on page 33).
- Device with Wi-Fi interface available on request.
- All these versions are equipped with the special functions ATF (acoustic transmission factor) and DF (density factor).

Clamp and pipe size	Surface quality		Clamp dimensions D2 x s; D3 (s = wall thickness)	Maximal flow rate	Display	Certifications		Article no.				
	Housing and outer surface of measurement tube	Inner surface of measurement tube										
[mm]	[µm]	[µm]	[mm]	[m³/h]		3A (28-06)	EHEDG ^{1,2)}					
Version without industrial communication (2 cable glands ^{2,)} M20x1.5 + 1 × 5 pin M12 male connector), operating voltage of 12...35 V DC												
08	Ra < 1.6	Ra < 0.8	13.5 × 1.6; 25.0	3	Yes	Yes	Yes	573126				
					No			573127				
		Ra < 0.4			Yes			573128				
					No			573129				
15		Ra < 0.8	21.3 × 1.6; 50.5	10	Yes		Yes	Yes	566187			
					No				566235			
									Yes	566191		
									No	566236		
		Ra < 0.4	21.3 × 1.6; 50.5		Yes			566195				
					No			566237				
								Yes	566199			
								No	566238			
		25	Ra < 0.8		33.7 × 2.0; 50.5			25	Yes	Yes	Yes	566188
									No			566192
			Ra < 0.4						Yes			566196
									No			566200
40		Ra < 0.8	48.3 × 2.0; 64.0	56	Yes			Yes	Yes		566189	
					No						566193	
		Ra < 0.4			Yes						566197	
					No						566201	
50		Ra < 0.8	60.3 × 2.0; 77.5	90	Yes				Yes		Yes	566190
					No							566194
		Ra < 0.4			Yes							566198
					No							566202

1.) The EHEDG compliance is only valid if used in combination with gaskets from Combifit International B.V.

2.) Cable gland in nickel plated brass

Clamp acc. to DIN 32676 series C (ASME BPE) process connection for pipe acc. to DIN 11866 series C (ASME BPE)

Note:

- To set up a device without a display, please use the USB-büS interface, Type 8920 (has to be ordered separately - see chapter “9. Product accessories” on page 26 and “10.7. Ordering chart accessories” on page 33).
- Device with Wi-Fi interface available on request.
- All these versions are equipped with the special functions ATF (acoustic transmission factor) and DF (density factor).

Clamp and pipe size	Surface quality		Clamp dimensions D2 x s; D3 (s = wall thickness)	Maximal flow rate	Display	Certifications			Article no.										
	Housing and outer surface of measurement tube	Inner surface of measurement tube				3A (28-06)	EHEDG ^{1,)}	UL											
[inch]	[µm]	[µm]	[mm]	[m³/h]															
Version without industrial communication (2 cable glands ^{2,)} M20x1.5+1×5 pin M12 male connector), operating voltage of 12...35 V DC																			
⅜	Ra<1.6	Ra<0.8	9.53x0.89; 25.0	1.7	Yes	Yes	Yes	No	573112										
					No				573113										
		Ra<0.4			Yes				573114										
					No				573115										
					Yes			Yes	573116										
½		Ra<0.8	12.07x1.65; 25.0	2.5	Yes			Yes	Yes	No	573119								
					No						573120								
		Ra<0.4			Yes						573121								
					No						573122								
					Yes					Yes	573123								
¾		Ra<0.8	19.05×1.65; 25.0	7	Yes					Yes	Yes	No	566203						
					No								566207						
		Ra<0.4			Yes								566211						
					No								566215						
					Yes							Yes	569675						
1		Ra<0.8	25.4×1.65; 50.5	14	Yes							Yes	Yes	No	566204				
					No										566208				
		Ra<0.4			Yes										566212				
					No										566216				
					Yes									Yes	569676				
1½		Ra<0.8	38.1×1.65; 50.5	35	Yes									Yes	Yes	No	566205		
					No												566209		
		Ra<0.4			Yes												566213		
					No												566217		
					Yes											Yes	569677		
2		Ra<0.8	50.8×1.65; 64.0	64 m³/h	Yes											Yes	Yes	No	566206
					No														566210
		Ra<0.4			Yes														566214
					No														566218
					Yes													Yes	569678

Clamp and pipe size	Surface quality		Clamp dimensions D2 x s; D3 (s = wall thickness)	Maximal flow rate	Display	Certifications			Article no.
	Housing and outer surface of measurement tube	Inner surface of measurement tube				3A (28-06)	EHEDG ^{1.)}	UL	
[inch]	[µm]	[µm]	[mm]	[m³/h]					
Version with industrial communication (Ethernet version, 2 x 4 pin M12 female connectors + 1 x 5 pin M12 male connector), operating voltage of 12...35 V DC									
3/8	Ra < 1.6	Ra < 0.4	9.53 x 0.89; 25.0	1.7	Yes	Yes	Yes	No	573117
								Yes	573118
1/2			12.07 x 1.65; 25.0	2.5				No	573124
								Yes	573125
3/4			19.05 x 1.65; 25.0	7				No	570444
								Yes	569679
1			25.4 x 1.65; 50.5	14				No	570445
								Yes	569680
1 1/2			38.1 x 1.65; 50.5	35				No	570446
								Yes	569681
2			50.8 x 1.65; 64.0	64				No	570447
								Yes	569682

1.) The EHEDG compliance is only valid if used in combination with gaskets from Combifit International B.V.

2.) Cable gland in nickel plated brass

Further versions on request		
	Process connection^{1.)} - For pipe DIN 11850: Clamp DIN 32676, Clamp DIN 11864-3, Flange DIN 11864-2 - For pipe ISO 1127: Clamp DIN 11864-3, Flange DIN 11864-2 - For pipe ASME BPE: Clamp DIN 11864-3, Flange DIN 11864-2 - For pipe SMS 3008: SMS 3017	Additional - Wi-Fi module (only for EU and north America) - Without density factor (DF) - Without acoustic transmission factor (ATF) - Ethernet module (EtherNet/IP, PROFINET, Modbus TCP/IP, ETHERCAT) - ATEX
	Electrical connection Cable gland in stainless steel	

1.) 3A & EHEDG certificate available

For any other versions, please use the product enquiry form at the end of this data sheet.

10.6. Ordering chart FLOWave S flowmeter

Clamp acc. to DIN 32676 series B (ISO 1127) process connection for pipe acc. to DIN 11866 series B (ISO 1127)

Note:

All these versions are equipped with the special functions ATF (acoustic transmission factor) and DF (density factor).

Clamp and pipe size	Surface quality		Clamp dimensions D2 x s; D3 (s = wall thickness)	Maximal flow rate	Certifications		Article no.
	Housing and outer surface of measurement tube	Inner surface of measurement tube					
[mm]	[µm]	[µm]	[mm]	[m³/h]	3A (28-06)	EHEDG ^{1.)}	
Electrical connection: 1 × 5 pin M12 male connector, operating voltage of 12...35 V DC							
08	Ra<1.6	Ra<0.8	13.5×1.6; 25.0	3	Yes	Yes	573716
		Ra<0.4					573717
15		Ra<0.8	21.3×1.6; 50.5 21.3×1.6; 34.0	10		Yes	573093
							573094
		Ra<0.4	21.3×1.6; 50.5 21.3×1.6; 34.0			Yes	573098
							573099
25		Ra<0.8	33.7×2.0; 50.5	25		Yes	573095
							573100
40		Ra<0.8	48.3×2.0; 64.0	56			573096
							573101
50	Ra<0.8	60.3×2.0; 77.5	90		573097		
					573102		
Electrical connection: 1 × 8 pin M12 male connector, operating voltage of 12...35 V DC							
08	Ra<1.6	Ra<0.8	13.5×1.6; 25.0	3	Yes	Yes	571780
		Ra<0.4					571781
15		Ra<0.8	21.3×1.6; 50.5 21.3×1.6; 34.0	10		Yes	571782
							571783
		Ra<0.4	21.3×1.6; 50.5 21.3×1.6; 34.0			Yes	571784
							571785
25		Ra<0.8	33.7×2.0; 50.5	25		Yes	571786
							571787
40		Ra<0.8	48.3×2.0; 64.0	56			571788
							571789
50	Ra<0.8	60.3×2.0; 77.5	90		571790		
					571791		

1.) The EHEDG compliance is only valid if used in combination with gaskets from Combifit International B.V.

Clamp acc. to DIN 32676 series C (ASME BPE) process connection for pipe acc. to DIN 11866 series C (ASME BPE)

Note:

All these versions are equipped with the special functions ATF (acoustic transmission factor) and DF (density factor).

Clamp and pipe size	Surface quality		Clamp dimensions D2 x s; D3 (s = wall thickness)	Maximal flow rate	Certifications			Article no.
	Housing and outer surface of measurement tube	Inner surface of measurement tube						
[inch]	[µm]	[µm]	[mm]	[m³/h]	3A (28-06)	EHEDG ¹⁾	UL	
Electrical connection: 1 × 5 pin M12 male connector, operating voltage of 12...35 V DC								
⅜	Ra < 1.6	Ra < 0.8	9.53 × 0.89; 25.0	1.7	Yes	Yes	No	573710
		Ra < 0.4						573711
½		Ra < 0.8	12.07 × 1.65; 25.0	2.5			Yes	573712
		Ra < 0.4					No	573713
¾		Ra < 0.8	19.05 × 1.65; 25.0	7				573714
		Ra < 0.4					Yes	573715
1		Ra < 0.8	25.4 × 1.65; 50.5	14			No	573085
		Ra < 0.4						573089
1½		Ra < 0.8	38.1 × 1.65; 50.5	35			Yes	573190
		Ra < 0.4					No	573086
2		Ra < 0.8	50.8 × 1.65; 64.0	64				573090
		Ra < 0.4					Yes	573191
Electrical connection: 1 × 8 pin M12 male connector, operating voltage of 12...35 V DC								
⅜	Ra < 1.6	Ra < 0.8	9.53 × 0.89; 25.0	1.7	Yes	Yes	No	571792
		Ra < 0.4						571793
½		Ra < 0.8	12.07 × 1.65; 25.0	2.5			Yes	571794
		Ra < 0.4					No	571795
¾		Ra < 0.8	19.05 × 1.65; 25.0	7				571796
		Ra < 0.4					Yes	571797
1		Ra < 0.8	25.4 × 1.65; 50.5	14			No	571798
		Ra < 0.4						571799
1½		Ra < 0.8	38.1 × 1.65; 50.5	35			Yes	571800
		Ra < 0.4					No	571801
2		Ra < 0.8	50.8 × 1.65; 64.0	64				571802
		Ra < 0.4					Yes	571803
Electrical connection: 1 × 8 pin M12 male connector, operating voltage of 12...35 V DC								
⅜	Ra < 1.6	Ra < 0.8	9.53 × 0.89; 25.0	1.7	Yes	Yes	No	571804
		Ra < 0.4						571805
½		Ra < 0.8	12.07 × 1.65; 25.0	2.5			Yes	571806
		Ra < 0.4					No	571807
¾		Ra < 0.8	19.05 × 1.65; 25.0	7				571808
		Ra < 0.4					Yes	571809
1		Ra < 0.8	25.4 × 1.65; 50.5	14			No	571810
		Ra < 0.4						571811
1½		Ra < 0.8	38.1 × 1.65; 50.5	35			Yes	571812
		Ra < 0.4					No	571813
2		Ra < 0.8	50.8 × 1.65; 64.0	64				571814
		Ra < 0.4					Yes	571815

1.) The EHEDG compliance is only valid if used in combination with gaskets from Combifit International B.V.

Further versions on request



Process connection^{1.)}

- For pipe DIN 11850: Clamp DIN 32676, Clamp DIN 11864-3, Flange DIN 11864-2
- For pipe ISO 1127: Clamp DIN 11864-3, Flange DIN 11864-2
- For pipe ASME BPE: Clamp DIN 11864-3, Flange DIN 11864-2
- For pipe SMS 3008: SMS 3017

1.) 3A & EHEDG certificate available

For any other versions, please use the product enquiry form at the end of this data sheet.

10.7. Ordering chart accessories

Description		Article no.
Display module, Type ME31		265468
Blind cover in stainless steel 304/1.4301		265467
	Unlocking magnetic key	690309
System Connect		
Type ME43 Gateway / Interface		
bÜS/Ethernet (PROFINET, EtherNet/IP, Modbus TCP, EtherCAT)		307390
bÜS/Profibus DP		307393
EDIP Accessories		
bÜS Stick Set		
	USB-bÜS-Interface Set 1, Type 8920. Detailed information can be found in chapter “9. Product accessories” on page 26.	772426
USB-bÜS Interface Set 2, Type 8920 (only bÜS Stick, cable and bÜS service cable)		772551
Connectors		
5 pin M12 female straight bÜS cable plug		772416
5 pin M12 male straight bÜS cable plug		772417
5 pin M12 female angled bÜS cable plug		772418
5 pin M12 male angled bÜS cable plug		772419
bÜS Y-connector, 5 pin M12 female to 5 pin M12 male and 5 pin M12 female		772420
bÜS Y-connector, 5 pin M12 female to 5 pin M12 male and 5 pin M12 female (power interrupt)		772421
bÜS adaptor M12 male A-coded - M12 male A-coded		772867
bÜS termination, 5 pin M12 male cable plug		772424
bÜS termination, 5 pin M12 female cable plug		772425
Adaptor cable, 8 pin M12 female - 5 pin M12 male		773286
Connectors with cable		
5 pin M12 female angled cable plug moulded on bÜS cable, with open leads		0,7 m 772626
5 pin M12 female straight cable plug moulded on bÜS cable, with open leads		1 m 772409
		3 m 772410
		5 m 772411
		10 m 772412
Micro USB and 5 pin M12 male straight cable plug moulded on bÜS cable		0,3 m 773254
8 pin M12 female straight cable plug moulded on bÜS cable, with open leads		2 m 919061
Extensions		
	5 pin M12 female and male straight cable plug moulded on bÜS cable, shielded	0,1 m 772492
		0,2 m 772402
		0,5 m 772403
		1 m 772404
		3 m 772405
		5 m 772406
		10 m 772407
		20 m 772408

Description	Article no.
Type 1573 Power Supplies	
1 A (NEC Class 2 Power Units)	772361 
2 A (NEC Class 2 Power Units)	772362 
3.8 A (NEC Class 2 Power Units)	772898 
10 A	772698 

Bürkert – Close to You

For up-to-date addresses
please visit us at
www.burkert.com

DTS 1000270652 EN Version: O Status: RL (released | freigegeben | valide) printed: 25.01.2021

Austria
Belgium
Czech Republic
Denmark
Finland
France
Germany
Italy
Netherlands

Norway
Poland
Spain
Sweden
Switzerland
Turkey
United Kingdom

Russia

Canada
USA

Brazil
Uruguay

South Africa

United
Arab
Emirates

Australia
New Zealand

China
Hong Kong
India
Japan
Korea
Malaysia
Philippines
Singapore
Taiwan

Product Enquiry Form - FLOWave SAW flowmeter

Thank you for your interest in our products! In order to provide you with optimum advice, please fill out the following form and send it to your **Bürkert representative** or e-mail address: info@buerkert.com. All information submitted will of course be kept strictly confidential.

Note: The interactive functions of this PDF may be restricted depending on the PDF reader used.

Personal Information			
Company		Contact person	
Customer no.		Department	
Street		Country / Postcode / Town	
Telephone no.		Email	

Delivery	
Quantity	Required delivery date

Operating data			
Function (Function of the flowmeter in the process / process description)			
Type of medium	Fluid		
Process fluid			
Flow rate (Q) ^{1.)}	Min.	Max.	Unit
Temperature	Min.	Max.	Unit
Absolute pressure	Min.	Max.	Unit
Viscosity	Min.	Max.	Unit
Density	Min.	Max.	Unit

1.) Standard unit: Fluid Q = m³/h

Process connection						
Pipe diameter DN	08 3/8"	10 1/2"	15 3/4"	25 1"	40 1 1/2"	50 2"
Connection ^{1.)}	Pipe DIN 11850	Clamp DIN 32676	Clamp DIN 11864-3	Flange DIN 11864-2		
	Pipe ISO 1127	Clamp DIN 32676	Clamp DIN 11864-3	Flange DIN 11864-2		
	Pipe ASME BPE	Clamp DIN 32676	Clamp DIN 11864-3	Flange DIN 11864-2		
	Pipe SMS 3008	SMS 3017				

1.) 3A & EHEDG certificate available

Additional configuration			
Surface finish (inner surface)	Ra < 0.8 µm (30 µin.)		Ra < 0.4 µm (15 µin.)
FLOWave L Electrical connection	Cable glands and M12 male connector (A-coded), in nickel plated brass (standard version)	Cable glands and M12 male connector (A-coded), in stainless steel (Full stainless steel or ATEX version)	M12 female connectors (D-coded) and M12 male connector (A-coded) in stainless steel (Ethernet version)
FLOWave S Electrical connection	5 pin M12 male connector (A-coded) in stainless steel (bÜS version)		8 pin M12 male connector (A-coded) in stainless steel (version with 2 configurable outputs (DO/AO))
Display module	With		Without
Wi-Fi module (only for EU and north America)	With		Without
Ethernet protocols	Modbus TCP EtherNet/IP	PROFINET EtherCAT®	Without
Special functions	With density factor (DF) With acoustic transmission factor (ATF)		Without density factor (DF) Without acoustic transmission factor (ATF)
Certification	UL listed 1 + CULus	ATEX	Without

Certification
FDA certificate (included in delivery)
Inspection certificate 3.1 acc. to EN 10204 (included in delivery)
Certification of compliance ASME BPE (included in delivery)
Calibration certificate (included in delivery)
EHEDG - TYPE EL-CLASS I ^{1.)} (included in delivery)
3A -28-06 (included in delivery)
USP class VI declaration
ECR1935/2004 declaration
EAC declaration of conformity
Test report 2.2 acc. to EN 10204 (article no. 803722)
Certification of conformity for the surface quality DIN 4762; EN ISO 4287; EN ISO 4288 (article no. 804175)
Certification of conformity for passivation and electropolishing processes (article no. 444900)
MTBF (Mean Time Between Failures) manufacturer declaration

1.) The EHEDG compliance is only valid if used in combination with gaskets from Combifit International B.V.

Note: If a certification which is not included in delivery with the FLOWave is requested, please order it separately. If you want to order one or more later, please contact your Bürkert office.

Additional Requirements / Comment